

MEGA-WAX HT

```
(function() {  
var po = document.createElement('script'); po.type = 'text/javascript'; po.async = true;  
po.src="https://apis.google.com/js/plusone.js";  
var s = document.getElementsByTagName('script')[0]; s.parentNode.insertBefore(po, s);  
})();
```

MEGA presents the new
WaX-HT GC column ,

the only Carbowax column that can reach 300Â°C (even in isothermal mode)!

Contact us for more information and details . Read the "LCGC -Europe" February 2010 issue; a technical article shows the performances of this new column applied to FAST-GC and GCxGC.

[Click here to read the online free article.](#)